

# HC38-38F-B Cut Sheet



NITRA pneumatic quick disconnect fitting, automatic coupling, chrome-plated steel body, (1) 3/8in female NPT to (1) 3/8in industrial interchange.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HC38-38F-B>

## Technical Specifications

|                          |   |
|--------------------------|---|
| Brand                    | NITRA   |
| Item                     | Fitting   |
| Working Fluid            | Air or inert gas  |
| Fitting Connection Type  | Quick disconnect  |
| Fitting Type             | Automatic coupling  |
| Body Material            | Chrome-plated steel                                       |
| Fitting Measurement Type | SAE   |
| Connection               | (1) 3/8in female NPT and (1) 3/8in industrial interchange |
| Operating Pressure       | 150 psi   |
| Operating Temperature    | 32 to 150 deg F   |

## Agency Approvals

|                      |  |
|----------------------|--|
| UL Listed File #     | None                                   |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CE                   | None                                   |
| CSA File #           | None                                   |
| RoHS Status          | No                                     |
| EU REACH             | <a href="#">View EU REACH document</a> |