

# HCP14-38M-L Cut Sheet



NITRA pneumatic quick disconnect fitting, coupling plug, steel body, (1) 3/8in male NPT to (1) 1/4in Truflate.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HCP14-38M-L>

## Technical Specifications

|                                 |   |
|---------------------------------|---|
| <b>Brand</b>                    | NITRA                                     |
| <b>Item</b>                     | Fitting                                   |
| <b>Working Fluid</b>            | Air or inert gas                          |
| <b>Fitting Connection Type</b>  | Quick disconnect                          |
| <b>Fitting Type</b>             | Coupling plug                             |
| <b>Body Material</b>            | Steel                                     |
| <b>Fitting Measurement Type</b> | SAE                                       |
| <b>Connection</b>               | (1) 3/8in male NPT and (1) 1/4in Truflate |
| <b>Operating Pressure</b>       | 150 psi                                   |
| <b>Operating Temperature</b>    | 32 to 150 deg F                           |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | None                                   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |