

HEE-00-3A Cut Sheet



AutomationDirect photoelectric sensor, tubular, threaded, stainless steel housing, through-beam emitter, infrared, 1m sensing distance, 10-30 VDC operating voltage, 2-wire, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HEE-00-3A>

Technical Specifications

Brand	AutomationDirect	Operating Voltage	10-30 VDC
Item	Photoelectric sensor	Number of Wires	2
Shape	Tubular	Sensing Distance	1m
Barrel Type	Threaded	Switching Frequency	10 kHz
Housing Size	8mm diameter x 49mm body	Light Emission (NP)	Infrared
IP Rating	IP67	Cable Length	3.2ft/1m
Housing Material	Stainless steel	Connection	Pigtail
Sensing Method	Through-beam emitter	Conductor Size	26 AWG

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document