

HER-CP-3A Cut Sheet



AutomationDirect photoelectric sensor, tubular, threaded, stainless steel housing, through-beam receiver, 1m sensing distance, 10-30 VDC operating voltage, light-on, PNP, 3-wire, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HER-CP-3A>

Technical Specifications

Brand	AutomationDirect
Item	Photoelectric sensor
Shape	Tubular
Barrel Type	Threaded
Housing Size	8mm diameter x 49mm body
IP Rating	IP67
Housing Material	Stainless steel
Sensing Method	Through-beam receiver
Operating Voltage	10-30 VDC

Number of Wires	3
Switching Output	PNP
Sensing Distance	1m
Operation Mode	Light-on
Switching Frequency	10 kHz
Cable Length	3.2ft/1m
Connection	Pigtail
Conductor Size	26 AWG

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document