

HG-201D-00-K Cut Sheet



Master Appliance D-Series heat gun, 400 deg F, 120 VAC operating voltage, 600W. Non-slip reinforced stand, (3) attachments (heat shrink, spreader, reducer), plastic carrying case included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HG-201D-00-K>

Technical Specifications

Brand	Master Appliance
Series	D-Series
Item	Heat gun
Maximum Tip Temperature	400 deg F
Flow Rating	27 CFM
Operating Voltage	120 VAC
Amperage Rating	5.0A
Power Rating	600W
Handle Material	Plastic
Cord Length	6ft
Switch Type	3 position switch (Hot-Cool-Off)
Includes	Non-slip reinforced stand, (3) attachments (heat shrink, spreader, reducer), plastic carrying case

Agency Approvals

UL Listed File #	E40970
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document
Other	RoHS Statement