

# HG-301D Cut Sheet



Master Appliance D-Series heat gun, 800 deg F, 120 VAC operating voltage, 1440W. Non-slip reinforced stand included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HG-301D>

## Technical Specifications

<b>Brand</b>	Master Appliance
<b>Series</b>	D-Series
<b>Item</b>	Heat gun
<b>Maximum Tip Temperature</b>	800 deg F
<b>Flow Rating</b>	27 CFM
<b>Operating Voltage</b>	120 VAC
<b>Amperage Rating</b>	12.0A
<b>Power Rating</b>	1440W
<b>Handle Material</b>	Plastic
<b>Cord Length</b>	6ft
<b>Switch Type</b>	3 position switch (Hot-Cool-Off)
<b>Includes</b>	Non-slip reinforced stand

## Agency Approvals

<b>UL Listed File #</b>	E40970
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>