


HGR-47-010-C Cut Sheet



IronHorse heavy-duty helical gearbox, 10:1 ratio, 182/4TC-Face input, inline, 1.25in diameter output shaft, nominal 3hp at 1.0 SF, 1140 lb-in mechanical output torque, Type-47 frame, cast iron housing, foot mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HGR-47-010-C>

Technical Specifications

Brand	IronHorse
Item	Gearbox
Application	General purpose
Duty Rating	Heavy-duty
Gearbox Type	Helical
Gear Ratio	10:1
Speed Rating	1750rpm input / 155rpm output
Input Configuration	182/4TC-Face
Input Power Rating	Nominal 3hp at 1.0 SF
Output Configuration	Inline
Gearbox Output Shaft Diameter	1.25in
Mechanical Output Torque	1140 lb-in
Thermal Output Torque	1140 lb-in
Frame	Type-47
Housing Material	Cast iron
Mounting	Foot
Includes	Motor mounting hardware
Finish	Anti-corrosion primer and paint
Lubrication Type	Pre-filled with HD320 mineral oil
Oil Seal Type	Double-lip

Agency Approvals

RoHS Status	No
EU REACH	View EU REACH document