

# HGR-87-040-C Cut Sheet



IronHorse heavy-duty helical gearbox, 40:1 ratio, 182/4TC-Face input, inline, 2.125in diameter output shaft, nominal 5hp at 1.0 SF, 6240 lb-in mechanical output torque, Type-87 frame, cast iron housing, foot mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HGR-87-040-C>

## Technical Specifications

<b>Brand</b>	IronHorse
<b>Item</b>	Gearbox
<b>Application</b>	General purpose
<b>Duty Rating</b>	Heavy-duty
<b>Gearbox Type</b>	Helical
<b>Gear Ratio</b>	40:1
<b>Speed Rating</b>	1750rpm input / 46rpm output
<b>Input Configuration</b>	182/4TC-Face
<b>Input Power Rating</b>	Nominal 5hp at 1.0 SF
<b>Output Configuration</b>	Inline
<b>Gearbox Output Shaft Diameter</b>	2.125in
<b>Mechanical Output Torque</b>	6240 lb-in
<b>Thermal Output Torque</b>	6240 lb-in
<b>Frame</b>	Type-87
<b>Housing Material</b>	Cast iron
<b>Mounting</b>	Foot
<b>Includes</b>	Motor mounting hardware
<b>Finish</b>	Anti-corrosion primer and paint
<b>Lubrication Type</b>	Pre-filled with HD320 mineral oil
<b>Oil Seal Type</b>	Double-lip

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>