

HJ444HLP Cut Sheet



Hammond enclosure, NEMA 3R/4/12/13, 4 x 4 x 4in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, single-door, stainless steel clamps.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HJ444HLP>

Technical Specifications

Brand	Hammond	Dual Access	No
Item	Enclosure	Knockouts	No
Slope Top	No	Bottom Gland Plate	No
3-Piece Assembly	No	Material	Carbon steel
Vented	No	Color	ANSI 61 gray
NEMA Rating	3R/4/12/13	Finish	Powder coat
IP Rating	IP66	Cover Type	Single-door
Nominal Enclosure Dimensions	4 x 4 x 4in (HxWxD)	Hinge Type	Continuous hinge
Enclosure Height	4.31in	Number of Hinges Per Door	1
Enclosure Width	4.31in	Latch Type	Stainless steel clamps
Enclosure Depth	4.20in	Number Of Latches	1
Mounting	Wall	Shelf	No
Integral Mounting Feet	No	Padlockable	No
Integral Mounting Flange	Yes	Keylocking	No

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR21001
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/HJ444HLP.pdf>
See store item page for other formats.