

# HL3096N-54-900-24 Cut Sheet



Dold force guided relay, 35mm DIN rail mount, finger-safe, 24 VDC coil voltage, 6PST, (4) N.O., (2) N.C., 5A contact rating, 14-pin, LED indicator(s), diode protection.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HL3096N-54-900-24>

## Technical Specifications

<b>Brand</b>	Dold
<b>Item</b>	Relay
<b>Relay Type</b>	Force guided
<b>Mounting</b>	35mm DIN rail
<b>Relay Housing Type</b>	Finger-safe
<b>Coil Voltage</b>	24 VDC
<b>Relay Configuration</b>	6PST
<b>Output Type</b>	(4) N.O., (2) N.C.
<b>Contact Rating</b>	5A
<b>Connector Type</b>	14-pin
<b>Indicator</b>	LED
<b>Protection Type(s)</b>	diode

## Agency Approvals

<b>UL Listed File #</b>	E146415
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/HL3096N-54-900-24.pdf>  
See store item page for other formats.