

HL3096N-54-900-24 Cut Sheet



Dold force guided relay, 35mm DIN rail mount, finger-safe, 24 VDC coil voltage, 6PST, (4) N.O., (2) N.C., 5A contact rating, 14-pin, LED indicator(s), diode protection.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HL3096N-54-900-24>

Technical Specifications

Brand	Dold
Item	Relay
Relay Type	Force guided
Mounting	35mm DIN rail
Relay Housing Type	Finger-safe
Coil Voltage	24 VDC
Relay Configuration	6PST
Output Type	(4) N.O., (2) N.C.
Contact Rating	5A
Connector Type	14-pin
Indicator	LED
Protection Type(s)	diode

Agency Approvals

UL Listed File #	E146415
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document