

HLM-174052 Cut Sheet



IDEM safety limit switch, plunger with stainless steel roller, (2) N.C. safety output(s), (2) N.O. monitoring output(s), slow action break before make, die-cast zinc aluminum, 1/2in female NPT conduit.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HLM-174052>

Technical Specifications

Brand	IDEM
Item	Safety limit switch
Switch Type	IEC
Actuator Type	Plunger with stainless steel roller
Head Type	90-degree adjustable
Safety Output Type	(2) N.C.
Monitoring Output Type	(2) N.O.
Action	Slow action break before make
Reset	No
Body Width	40mm
Material	Die-cast zinc aluminum
IP Rating	IP67
Connection	1/2in female NPT conduit

Agency Approvals

UL Listed File #	E258676
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document