

HLM-SS-175102 Cut Sheet



IDEM safety limit switch, stainless steel plunger, (2) N.C. safety output(s), (2) N.O. monitoring output(s), slow action break before make, 316 stainless steel, 1/2in female NPT conduit.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HLM-SS-175102>

Technical Specifications

Brand	IDEM
Item	Safety limit switch
Switch Type	IEC
Actuator Type	Stainless steel plunger
Head Type	90-degree adjustable
Safety Output Type	(2) N.C.
Monitoring Output Type	(2) N.O.
Action	Slow action break before make
Reset	No
Body Width	41.6mm
Material	316 stainless steel
IP Rating	IP67 IP69K
Connection	1/2in female NPT conduit

Agency Approvals

UL Listed File #	E258676
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document