

# HLM-SS-175302 Cut Sheet



IDEM safety limit switch, side rotary adjustable lever with stainless steel roller, (2) N.C. safety output(s), (2) N.O. monitoring output(s), slow action break before make, 316 stainless steel, (1) 1/2in female NPT conduit.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HLM-SS-175302>

## Technical Specifications

Brand	IDEM
Item	Safety limit switch
Switch Type	IEC
Actuator Type	Side rotary adjustable lever with stainless steel roller
Head Type	90-degree adjustable
Safety Output Type	(2) N.C.
Monitoring Output Type	(2) N.O.
Action	Slow action break before make
Reset	No
Body Width	41.6mm
Material	316 stainless steel
IP Rating	IP67 IP69K
Connection	(1) 1/2in female NPT conduit

## Agency Approvals

UL Listed File #	E258676
CE	<a href="#">View CE declarations</a>
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/HLM-SS-175302.pdf>  
See store item page for other formats.