

HLM-SS-175311 Cut Sheet



IDEM safety limit switch, side rotary adjustable lever with stainless steel roller, (1) N.C. safety output(s), (1) N.O. monitoring output(s), snap action, 316 stainless steel, 1/2in female NPT conduit.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HLM-SS-175311>

Technical Specifications

| | |
|------------------------|--|
| Brand | IDEM |
| Item | Safety limit switch |
| Switch Type | IEC |
| Actuator Type | Side rotary adjustable lever with stainless steel roller |
| Head Type | 90-degree adjustable |
| Safety Output Type | (1) N.C. |
| Monitoring Output Type | (1) N.O. |
| Action | Snap action |
| Reset | No |
| Body Width | 41.6mm |
| Material | 316 stainless steel |
| IP Rating | IP67 IP69K |
| Connection | 1/2in female NPT conduit |

Agency Approvals

| | |
|------------------|--|
| UL Listed File # | E258676 |
| CE | View CE declarations |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |