

# HMC-100A30-22-BL Cut Sheet



IronHorse IEC contactor, 100A, (3) N.O. power poles, (2) N.O./ (2) N.C. auxiliary contacts, 24 VAC (50/60Hz) coil voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HMC-100A30-22-BL>

## Technical Specifications

|                           |                        |
|---------------------------|------------------------|
| <b>Brand</b>              | IronHorse              |
| <b>Item</b>               | Contactor              |
| <b>Contactor Type</b>     | IEC                    |
| <b>Actuator Type</b>      | Magnetic               |
| <b>Amperage Rating</b>    | 100A                   |
| <b>Power Poles</b>        | (3) N.O.               |
| <b>Auxiliary Contacts</b> | (2) N.O./ (2) N.C.     |
| <b>Coil Voltage</b>       | 24 VAC (50/60Hz)       |
| <b>Horsepower Rating</b>  | 75hp                   |
| <b>SCCR Rating</b>        | 10kA SCCR              |
| <b>Mounting</b>           | 35mm DIN rail or panel |

## Agency Approvals

|                         |  |
|-------------------------|--|
| <b>UL Listed File #</b> | E191059                                |
| <b>CE</b>               | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>       | None                                   |
| <b>RoHS Status</b>      | Yes (See CE Doc)                       |
| <b>EU REACH</b>         | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/HMC-100A30-22-BL.pdf>  
See store item page for other formats.