

HMC-150A30-22-FL Cut Sheet



IronHorse IEC contactor, 150A, (3) N.O. power poles, (2) N.O./ (2) N.C. auxiliary contacts, 100-240 VAC (50/60Hz)/100-200 VDC coil voltage, low consumption electronic.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HMC-150A30-22-FL>

Technical Specifications

Brand	IronHorse
Item	Contactor
Contactor Type	IEC
Actuator Type	Magnetic
Amperage Rating	150A
Power Poles	(3) N.O.
Auxiliary Contacts	(2) N.O./ (2) N.C.
Coil Voltage	100-240 VAC (50/60Hz)/100-200 VDC
Coil Type	Low consumption electronic
Horsepower Rating	100hp
SCCR Rating	10kA SCCR
Mounting	35mm DIN rail or panel

Agency Approvals

UL Listed File #	E191059
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/HMC-150A30-22-FL.pdf>
See store item page for other formats.