

HMC-40A30-22-CS Cut Sheet



IronHorse IEC contactor, 40A, (3) N.O. power poles, (2) N.O./ (2) N.C. auxiliary contacts, 230 VAC (50/60Hz) coil voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HMC-40A30-22-CS>

Technical Specifications

Brand	IronHorse
Item	Contactor
Contactor Type	IEC
Actuator Type	Magnetic
Amperage Rating	40A
Power Poles	(3) N.O.
Auxiliary Contacts	(2) N.O./ (2) N.C.
Coil Voltage	230 VAC (50/60Hz)
Horsepower Rating	30hp
SCCR Rating	5kA SCCR
Mounting	35mm DIN rail or panel

Agency Approvals

UL Listed File #	E191059
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/HMC-40A30-22-CS.pdf>
See store item page for other formats.