

HMC-50A30-22-CL Cut Sheet



IronHorse IEC contactor, 50A, (3) N.O. power poles, (2) N.O./ (2) N.C. auxiliary contacts, 230 VAC (50/60Hz) coil voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HMC-50A30-22-CL>

Technical Specifications

| | |
|---------------------------|------------------------|
| Brand | IronHorse |
| Item | Contactor |
| Contactor Type | IEC |
| Actuator Type | Magnetic |
| Amperage Rating | 50A |
| Power Poles | (3) N.O. |
| Auxiliary Contacts | (2) N.O./ (2) N.C. |
| Coil Voltage | 230 VAC (50/60Hz) |
| Horsepower Rating | 40hp |
| SCCR Rating | 5kA SCCR |
| Mounting | 35mm DIN rail or panel |

Agency Approvals

| | |
|-------------------------|--|
| UL Listed File # | E191059 |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/HMC-50A30-22-CL.pdf>
See store item page for other formats.