# HMMP-32HR-26 Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

IronHorse manual motor protector, rotary, 26A, thermal overload, 18 -26A adjustable, 338A instantaneous trip rating, 45mm frame.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/HMMP-32HR-26

## Technical Specifications

| | |
|---|---|
| **Brand** | IronHorse |
| **Item** | Motor protector |
| **Starter Type** | Manual |
| **Actuator Type** | Rotary |
| **Amperage Rating** | 26A |
| **Voltage Rating** | 600 VAC |
| **Horsepower Rating** | 15hp |
| **Relay Type** | Thermal overload |
| **Operation Type** | Bi-metallic |
| **Full Load Amperage Range** | 18 -26A adjustable |
| **Instantaneous Trip Rating** | 338A |
| **Number of Poles** | 3 |
| **Power Poles** | (3) N.O. |

| | |
|---|---|
| **Trip Class** | Trip Class 10 |
| **Phase Loss Sensitive** | Yes |
| **Ground Fault Protection** | No |
| **SCCR Rating** | 30kA SCCR |
| **UL Rating** | UL 508 rated |
| **Frame** | 45mm |
| **Mounting** | 35mm DIN rail |
| **Connection** | Screw terminal |
| **Additional Information** | For UL Type E listing, power terminal HPX1-PTBE-MP and short circuit alarm contact block HPX1-MALM11-S must be added. Suitable as a motor disconnect |

## Agency Approvals

| | |
|---|---|
| **UL Listed File #** | E195426, E531281 |
| **CE** | View CE declarations |
| **CSA File #** | None |
| **RoHS Status** | Yes (See CE Doc) |
| **EU REACH** | View EU REACH document |

## Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/HMMP-32HR-26.pdf
See store item page for other formats.