

HMMP-63HR-32 Cut Sheet



IronHorse manual motor protector, rotary, 32A, thermal overload, 22-32A adjustable, 416A instantaneous trip rating, 55mm frame.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HMMP-63HR-32>

Technical Specifications

| | |
|----------------------------------|-------------------|
| Brand | IronHorse |
| Item | Motor protector |
| Starter Type | Manual |
| Actuator Type | Rotary |
| Amperage Rating | 32A |
| Voltage Rating | 600 VAC |
| Horsepower Rating | 20hp |
| Relay Type | Thermal overload |
| Operation Type | Bi-metallic |
| Full Load Amperage Range | 22-32A adjustable |
| Instantaneous Trip Rating | 416A |
| Number of Poles | 3 |

| | |
|--------------------------------|--|
| Power Poles | (3) N.O. |
| Trip Class | Trip Class 10 |
| Phase Loss Sensitive | Yes |
| Ground Fault Protection | No |
| SCCR Rating | 50kA SCCR |
| UL Rating | UL 508 rated |
| Frame | 55mm |
| Mounting | 35mm DIN rail or panel |
| Connection | Screw terminal |
| Additional Information | For UL Type E listing, short circuit alarm contact block HPX1-MALM11-S must be added. Suitable as a motor disconnect |

Agency Approvals

| | |
|-------------------------|--|
| UL Listed File # | E195426, E531281 |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/HMMP-63HR-32.pdf>
See store item page for other formats.