

# HN12C12-12YEL Cut Sheet



NITRA pneumatic coiled hose, nylon 12, yellow, 1/2in inside diameter, 0.625in outside diameter, (2) 1/2in male NPT nickel-plated brass swivel fittings, 10ft working length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HN12C12-12YEL>

## Technical Specifications

<b>Brand</b>	NITRA
<b>Item</b>	Pneumatic Coiled hose
<b>Material</b>	Nylon 12
<b>Color</b>	Yellow
<b>Inside Diameter</b>	1/2in
<b>Outside Diameter</b>	0.625in
<b>Connection</b>	(2) 1/2in male NPT nickel-plated brass swivel fittings
<b>Working Length</b>	10ft working length
<b>Operating Pressure</b>	170 psi
<b>Operating Temperature</b>	-60 to +200 deg F

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>