

# HN12C12-12YEL Cut Sheet



NITRA pneumatic coiled hose, nylon 12, yellow, 1/2in inside diameter, 0.625in outside diameter, (2) 1/2in male NPT nickel-plated brass swivel fittings, 10ft working length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HN12C12-12YEL>

## Technical Specifications

Brand	NITRA
Item	Coiled hose
Working Fluid	Air or inert gas
Material	Nylon 12
Color	Yellow
Inside Diameter	1/2in
Outside Diameter	0.625in
Connection	(2) 1/2in male NPT nickel-plated brass swivel fittings
Working Length	10ft working length
Operating Pressure	170 psi
Operating Temperature	-60 to +200 deg F

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/HN12C12-12YEL.pdf>  
See store item page for other formats.