

HN14C14-50YEL Cut Sheet



NITRA pneumatic coiled hose, nylon 12, yellow, 1/4in inside diameter, 0.3125in outside diameter, (2) 1/4in male NPT nickel-plated brass swivel fittings, 40ft working length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HN14C14-50YEL>

Technical Specifications

Brand	NITRA
Item	Coiled hose
Working Fluid	Air or inert gas
Material	Nylon 12
Color	Yellow
Inside Diameter	1/4in
Outside Diameter	0.3125in
Connection	(2) 1/4in male NPT nickel-plated brass swivel fittings
Working Length	40ft working length
Operating Pressure	250 psi
Operating Temperature	-60 to +200 deg F

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/HN14C14-50YEL.pdf>
See store item page for other formats.