

HN38C38-50YEL Cut Sheet



NITRA pneumatic coiled hose, nylon 12, yellow, 3/8in inside diameter, 0.47in outside diameter, (2) 3/8in male NPT nickel-plated brass swivel fittings, 42ft working length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HN38C38-50YEL>

Technical Specifications

Brand	NITRA
Item	Coiled hose
Working Fluid	Air or inert gas
Material	Nylon 12
Color	Yellow
Inside Diameter	3/8in
Outside Diameter	0.47in
Connection	(2) 3/8in male NPT nickel-plated brass swivel fittings
UV stabilized	No
Working Length	42ft working length
Operating Pressure	225 psi
Operating Temperature	-60 to +200 deg F

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/HN38C38-50YEL.pdf>
See store item page for other formats.