

HN4FM604812SS Cut Sheet



Hammond enclosure, NEMA 3R/4X/12/13, 60 x 48 x 12in (HxWxD), floor mount, 304 stainless steel, #4 brush finish, 2-door, 3-point 316 stainless steel padlocking handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HN4FM604812SS>

Technical Specifications

Brand	Hammond	Integral Mounting Flange	No
Item	Enclosure	Dual Access	No
Subpanel	Subpanel included	Knockouts	No
Slope Top	No	Bottom Gland Plate	No
3-Piece Assembly	No	Material	304 stainless steel
Vented	No	Finish	#4 brush
NEMA Rating	3R/4X/12/13	Cover Type	2-door
IP Rating	IP66	Hinge Type	Continuous hinge
Nominal Enclosure Dimensions	60 x 48 x 12in (HxWxD)	Number of Hinges Per Door	1
Enclosure Height	60.13in	Latch Type	3-point 316 stainless steel padlocking handle
Enclosure Width	48.06in	Number Of Latches	2
Enclosure Depth	13.88in	Shelf	No
Mounting	Floor	Padlockable	Yes
Integral Mounting Feet	No	Keylocking	No

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR21001
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/HN4FM604812SS.pdf>
See store item page for other formats.