

HN4FM606012S16 Cut Sheet



Hammond enclosure, NEMA 3R/4X/12/13, 60 x 60 x 12in (HxWxD), floor mount, 316 stainless steel, #4 brush finish, 2-door, 3-point 316 stainless steel padlocking handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HN4FM606012S16>

Technical Specifications

Brand	Hammond
Item	Enclosure
Subpanel	Subpanel included
Slope Top	No
3-Piece Assembly	No
Vented	No
NEMA Rating	3R/4X/12/13
IP Rating	IP66
Nominal Enclosure Dimensions	60 x 60 x 12in (HxWxD)
Enclosure Height	60.13in
Enclosure Width	60.06in
Enclosure Depth	13.88in
Mounting	Floor
Integral Mounting Feet	No

Integral Mounting Flange	No
Dual Access	No
Knockouts	No
Bottom Gland Plate	No
Material	316 stainless steel
Finish	#4 brush
Cover Type	2-door
Hinge Type	Continuous hinge
Number of Hinges Per Door	1
Latch Type	3-point 316 stainless steel padlocking handle
Number Of Latches	2
Shelf	No
Padlockable	Yes
Keylocking	No

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR21001
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/HN4FM606012S16.pdf>
See store item page for other formats.