

HN4WM304210S16 Cut Sheet



Hammond enclosure, NEMA 3R/4X/12/13, 30 x 42 x 10in (HxWxD), wall mount, 316 stainless steel, #4 brush finish, 2-door, 3-point 316 stainless steel padlocking handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HN4WM304210S16>

Technical Specifications

Brand	Hammond
Item	Enclosure
Subpanel	Subpanel included
Slope Top	No
NEMA Rating	3R/4X/12/13
IP Rating	IP66
Nominal Enclosure Dimensions	30 x 42 x 10in (HxWxD)
Enclosure Height	30.00in
Enclosure Width	42.00in
Enclosure Depth	11.09in
Mounting	Wall
Integral Mounting Feet	Yes

Integral Mounting Flange	No
Dual Access	No
Knockouts	No
Material	316 stainless steel
Finish	#4 brush
Cover Type	2-door
Hinge Type	Continuous hinge
Number of Hinges Per Door	1
Latch Type	3-point 316 stainless steel padlocking handle
Number Of Latches	2
Padlockable	Yes
Keylocking	No

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR21001
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document