

HP0400A6S Cut Sheet



Peninsular hydraulic cylinder, NFPA tie rod, 4in bore, 1-3/4in rod diameter, 6in stroke, double acting.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HP0400A6S>

Technical Specifications

Brand	Peninsular
Item	Cylinder
Working Fluid	Petroleum based hydraulic fluid
Cylinder Type	NFPA tie rod
Bore Diameter	4in
Stroke	6in
Port Size	SAE size -12 o-ring port
Action Type	Double acting
Body Material	Honed, chrome plated DOM steel tube
End Cap Material	Steel
Rod Material	Chrome-plated steel
Rod Diameter	1-3/4in
Rod Thread Size	1 1/4-12
Bushing Type	Ductile iron
Alternate ID	HP0 400x6AM-TNNN-TNNN-O

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/HP0400A6S.pdf>
See store item page for other formats.