

HP0400B12S Cut Sheet



Peninsular hydraulic cylinder, NFFA tie rod, 4in bore, 2in rod diameter, 12in stroke, double acting.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HP0400B12S>

Technical Specifications

Brand	Peninsular
Item	Cylinder
Working Fluid	Hydraulic
Cylinder Type	NFFA tie rod
Bore Diameter	4in
Stroke	12in
Port Size	SAE size -12 o-ring port
Action Type	Double acting
Magnetic Piston	No

Adjustable Cushions	No
Body Material	Honed, chrome plated DOM steel tube
End Cap Material	Steel
Rod Material	Chrome-plated steel
Rod Diameter	2in
Rod Thread Size	1-1/2-12 UNF
Bushing Type	Ductile iron
Maximum Operating Pressure	3000 psi
Manufacturer Part Number	HP0 400x12BM-TNNN-TNNN-0

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/HP0400B12S.pdf>
See store item page for other formats.