

HP0400B6S Cut Sheet



Peninsular hydraulic cylinder, NFPA tie rod, 4in bore, 2in rod diameter, 6in stroke, double acting.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HP0400B6S>

Technical Specifications

Brand	Peninsular
Item	Cylinder
Working Fluid	Petroleum based hydraulic fluid
Cylinder Type	NFPA tie rod
Bore Diameter	4in
Stroke	6in
Port Size	SAE size -12 o-ring port
Action Type	Double acting
Body Material	Honed, chrome plated DOM steel tube
End Cap Material	Steel
Rod Material	Chrome-plated steel
Rod Diameter	2in
Rod Thread Size	1 1/2-12
Bushing Type	Ductile iron
Alternate ID	HP0 400x6BM-TNNN-TNNN-O

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/HP0400B6S.pdf>
See store item page for other formats.