


# HP14C10CBL-QC Cut Sheet



NITRA pneumatic coiled hose, polyurethane, clear blue, 1/4in inside diameter, 0.375in outside diameter, 1/4in chrome plated steel quick-disconnect fittings, 8ft working length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HP14C10CBL-QC>

## Technical Specifications

<b>Brand</b>	NITRA
<b>Item</b>	Pneumatic Coiled hose
<b>Material</b>	Polyurethane
<b>Color</b>	Clear blue
<b>Inside Diameter</b>	1/4in
<b>Outside Diameter</b>	0.375in
<b>Connection</b>	1/4in chrome plated steel quick-disconnect fittings
<b>Working Length</b>	8ft working length
<b>Operating Pressure</b>	140 psi
<b>Operating Temperature</b>	-68 to +140 deg F

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>