

# HP16150B10S Cut Sheet



Peninsular hydraulic cylinder, NFPA tie rod, 1-1/2in bore, 1in rod diameter, 10in stroke, double acting, tapped end caps mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HP16150B10S>

## Technical Specifications

<b>Brand</b>	Peninsular
<b>Item</b>	Cylinder
<b>Working Fluid</b>	Petroleum based hydraulic fluid
<b>Cylinder Type</b>	NFPA tie rod
<b>Bore Diameter</b>	1-1/2in
<b>Stroke</b>	10in
<b>Port Size</b>	SAE size -8 o-ring port
<b>Mounting</b>	Tapped end caps

<b>Action Type</b>	Double acting
<b>Body Material</b>	Honed, chrome plated DOM steel tube
<b>End Cap Material</b>	Steel
<b>Rod Material</b>	Chrome-plated steel
<b>Rod Diameter</b>	1in
<b>Rod Thread Size</b>	3/4-16
<b>Bushing Type</b>	Ductile iron
<b>Alternate ID</b>	HP16 150x10BM-TNNN-TNNN-O

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/HP16150B10S.pdf>  
See store item page for other formats.