

HP16200B3S Cut Sheet



Peninsular hydraulic cylinder, NFPA tie rod, 2in bore, 1-3/8in rod diameter, 3in stroke, double acting, tapped end caps mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HP16200B3S>

Technical Specifications

Brand	Peninsular
Item	Cylinder
Working Fluid	Hydraulic
Cylinder Type	NFPA tie rod
Bore Diameter	2in
Stroke	3in
Port Size	SAE size -8 o-ring port
Mounting	Tapped end caps
Action Type	Double acting
Magnetic Piston	No

Adjustable Cushions	No
Body Material	Honed, chrome plated DOM steel tube
End Cap Material	Steel
Rod Material	Chrome-plated steel
Rod Diameter	1-3/8in
Rod Thread Size	1-14 UNS
Bushing Type	Ductile iron
Maximum Operating Pressure	3000 psi
Manufacturer Part Number	HP16 200x3BM-TNNN-TNNN-0

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/HP16200B3S.pdf>
See store item page for other formats.