

HP16250B2S Cut Sheet



Peninsular hydraulic cylinder, NFPA tie rod, 2-1/2in bore, 1-3/8in rod diameter, 2in stroke, double acting, tapped end caps mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HP16250B2S>

Technical Specifications

| | |
|----------------------|---------------------------------|
| Brand | Peninsular |
| Item | Cylinder |
| Working Fluid | Petroleum based hydraulic fluid |
| Cylinder Type | NFPA tie rod |
| Bore Diameter | 2-1/2in |
| Stroke | 2in |
| Port Size | SAE size -8 o-ring port |
| Mounting | Tapped end caps |

| | |
|-------------------------|-------------------------------------|
| Action Type | Double acting |
| Body Material | Honed, chrome plated DOM steel tube |
| End Cap Material | Steel |
| Rod Material | Chrome-plated steel |
| Rod Diameter | 1-3/8in |
| Rod Thread Size | 1-14 |
| Bushing Type | Ductile iron |
| Alternate ID | HP16 250x2BM-TNNN-TNNN-O |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/HP16250B2S.pdf>
See store item page for other formats.