

HPB106-1 Cut Sheet



Edison open power distribution block, 175A, 1-pole, line side: 1 opening accepts 2/0 AWG to 8 AWG, load side: 6 openings accept 4 AWG to 14 AWG, panel mount, UL 1953 listed.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HPB106-1>

Technical Specifications

Brand	Edison
Item	Power distribution block
Terminal Block Type	Open
Amperage Rating	175A
Number of Poles	1
Line Side Openings	1 opening accepts 2/0 AWG to 8 AWG
Load Side Openings	6 openings accept 4 AWG to 14 AWG
Mounting	Panel
SCCR Rating	200kA SCCR
UL Rating	UL 1953 listed
Additional Information	Suitable for branch and feeder circuits

Agency Approvals

UL Listed File #	E333541
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document
Other	None