

HPB312-3 Cut Sheet



Edison open power distribution block, 310A, 3-pole, line side:
1 opening accepts 350 MCM to 4 AWG, load side: 12 openings
accept 4AWG to 14 AWG, panel mount, UL 1953 listed.

For complete product information, please see this item on our
store at the following link:



<https://www.automationdirect.com/pn/HPB312-3>

Technical Specifications

Brand	Edison
Item	Power distribution block
Terminal Block Type	Open
Amperage Rating	310A
Number of Poles	3
Line Side Openings	1 opening accepts 350 MCM to 4 AWG
Load Side Openings	12 openings accept 4AWG to 14 AWG
Mounting	Panel
SCCR Rating	200kA SCCR
UL Rating	UL 1953 listed
Additional Information	Suitable for branch and feeder circuits

Agency Approvals

UL Listed File #	E333541
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document
Other	None

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/HPB312-3.pdf>
See store item page for other formats.