

HPGA073-120A2 Cut Sheet



SureGear high-precision strain wave gearbox, 120:1 ratio, inline, 16mm diameter output shaft, nominal output torque 30 N-m (266 lb-in), 1-stage, 73mm frame. For use with SureServo and SureServo2 SV(2)L-202(B) and SV(2)L-204(B) motors.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HPGA073-120A2>

Technical Specifications

| | |
|--------------------------------------|---|
| Brand | SureGear |
| Item | Gearbox |
| Application | High-precision |
| Gearbox Type | Strain wave |
| Gear Ratio | 120:1 |
| Output Configuration | Inline |
| Gearbox Output Shaft Diameter | 16mm |
| Nominal Output Torque | Nominal output torque 30 N-m (266 lb-in) |
| Number of Stages | 1 |
| Frame | 73mm |
| For Use With | SureServo and SureServo2 SV(2)L-202(B) and SV(2)L-204(B) motors |
| Includes | Motor mounting hardware and output shaft key |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |