

HPGA116-200A4 Cut Sheet



SureGear high-precision strain wave gearbox, 200:1 ratio, inline, 32mm diameter output shaft, nominal output torque 120 N-m (1062 lb-in), 1-stage, 116mm frame. For use with SureServo and SureServo2 SV(2)L-210(B) motors.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HPGA116-200A4>

Technical Specifications

| | |
|--------------------------------------|---|
| Brand | SureGear |
| Item | Gearbox |
| Application | High-precision |
| Gearbox Type | Strain wave |
| Gear Ratio | 200:1 |
| Output Configuration | Inline |
| Gearbox Output Shaft Diameter | 32mm |
| Nominal Output Torque | Nominal output torque 120 N-m (1062 lb-in) |
| Number of Stages | 1 |
| Frame | 116mm |
| For Use With | SureServo and SureServo2 SV(2)L-210(B) motors |
| Includes | Motor mounting hardware and output shaft key |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/HPGA116-200A4.pdf>
See store item page for other formats.