

HPGCN23-8025 Cut Sheet



SureGear high-precision strain wave gearbox, 80:1 ratio, inline, 0.5in diameter output shaft, nominal output torque 25 N-m (221 lb-in), 1-stage, NEMA 23 frame. For use with SureStep NEMA 23 motors.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HPGCN23-8025>

Technical Specifications

Brand	SureGear
Item	Gearbox
Application	High-precision
Gearbox Type	Strain wave
Gear Ratio	80:1
Output Configuration	Inline
Gearbox Output Shaft Diameter	0.5in
Nominal Output Torque	Nominal output torque 25 N-m (221 lb-in)
Number of Stages	1
Frame	NEMA 23
For Use With	SureStep NEMA 23 motors
Includes	Motor mounting hardware and output shaft key

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document