

# HPVC14-100BG Cut Sheet



NITRA pneumatic or water hose, hybrid PVC, polyester reinforced, black with green stripe, 1/4in inside diameter, 7/16in outside diameter, 100ft.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HPVC14-100BG>

## Technical Specifications

<b>Brand</b>	NITRA
<b>Item</b>	Pneumatic or water Hose
<b>Material</b>	Hybrid PVC
<b>Reinforcement</b>	Polyester
<b>Color</b>	Black with green stripe
<b>Inside Diameter</b>	1/4in
<b>Outside Diameter</b>	7/16in
<b>Working Length</b>	100ft
<b>Operating Pressure</b>	300 psi
<b>Operating Temperature</b>	-40 to 180 deg F

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>