

HPVC14-500BG Cut Sheet



NITRA pneumatic or water hose, hybrid PVC, polyester reinforced, black with green stripe, 1/4in inside diameter, 7/16in outside diameter, 500ft.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HPVC14-500BG>

Technical Specifications

| | |
|------------------------------|-------------------------|
| Brand | NITRA |
| Item | Pneumatic or water Hose |
| Material | Hybrid PVC |
| Reinforcement | Polyester |
| Color | Black with green stripe |
| Inside Diameter | 1/4in |
| Outside Diameter | 7/16in |
| Working Length | 500ft |
| Operating Pressure | 300 psi |
| Operating Temperature | -40 to 180 deg F |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |