

HPVC14-50BG2 Cut Sheet



NITRA pneumatic or water hose, hybrid PVC, polyester reinforced, black with green stripe, 1/4in inside diameter, 7/16in outside diameter, 1/4in male NPT nickel-plated brass rigid fittings, 50ft.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HPVC14-50BG2>

Technical Specifications

Brand	NITRA
Item	Pneumatic or water Hose
Material	Hybrid PVC
Reinforcement	Polyester
Color	Black with green stripe
Inside Diameter	1/4in
Outside Diameter	7/16in
Connection	1/4in male NPT nickel-plated brass rigid fittings
Working Length	50ft
Operating Pressure	300 psi
Operating Temperature	-40 to 180 deg F

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document