


HPVC38-500BG Cut Sheet



NITRA pneumatic or water hose, hybrid PVC, polyester reinforced, black with green stripe, 3/8in inside diameter, 9/16in outside diameter, 500ft.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HPVC38-500BG>

Technical Specifications

Brand	NITRA
Item	Pneumatic or water Hose
Material	Hybrid PVC
Reinforcement	Polyester
Color	Black with green stripe
Inside Diameter	3/8in
Outside Diameter	9/16in
Working Length	500ft
Operating Pressure	300 psi
Operating Temperature	-40 to 180 deg F

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document