

HPX1-AUX20-F Cut Sheet

IronHorse field installable auxiliary contact, front mount, (2) N.O. contact(s), 6A @ 120 VAC/0.22A @ 120 VDC, screw terminal. For use with HMMP-32H to HMMP-100H manual motor protectors.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HPX1-AUX20-F>

Technical Specifications

Brand	IronHorse
Item	Auxiliary contact
Field Installable	Yes
Mounting	Front
Contact Type	(2) N.O.
Amperage Rating	6A @ 120 VAC/0.22A @ 120 VDC
Connection	Screw terminal
For Use With	HMMP-32H to HMMP-100H manual motor protectors

Agency Approvals

UL Listed File #	E195426, E531281
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/HPX1-AUX20-F.pdf>
See store item page for other formats.