

# HPX1-MALM11-S Cut Sheet



IronHorse field installable short circuit alarm contact, left side mount, (1) N.O./ (1) N.C. contact(s), 6A @ 120 VAC/0.55A @ 120 VDC, screw terminal. For use with HMMP-32H to HMMP-100H manual motor protectors.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HPX1-MALM11-S>

## Technical Specifications

<b>Brand</b>	IronHorse
<b>Item</b>	Short circuit alarm contact
<b>Field Installable</b>	Yes
<b>Mounting</b>	Left side
<b>Contact Type</b>	(1) N.O./ (1) N.C.
<b>Amperage Rating</b>	6A @ 120 VAC/0.55A @ 120 VDC
<b>Connection</b>	Screw terminal
<b>For Use With</b>	HMMP-32H to HMMP-100H manual motor protectors
<b>Additional Information</b>	Indicates a short-circuit trip only

## Agency Approvals

<b>UL Listed File #</b>	E195426, E531281
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>