

HPX2-ALM11-S Cut Sheet



IronHorse field installable alarm contact, left side mount, (1) N.O./ (1) N.C. contact(s), 6A @ 120 VAC/0.55A @ 120 VDC, screw terminal. For use with HMMP-63H and HMMP-100H manual motor protectors.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HPX2-ALM11-S>

Technical Specifications

Brand	IronHorse
Item	Alarm contact
Field Installable	Yes
Mounting	Left side
Contact Type	(1) N.O./ (1) N.C.
Amperage Rating	6A @ 120 VAC/0.55A @ 120 VDC
Connection	Screw terminal
For Use With	HMMP-63H and HMMP-100H manual motor protectors
Additional Information	Indicates a short-circuit or thermal trip

Agency Approvals

UL Listed File #	E195426, E531281
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/HPX2-ALM11-S.pdf>
See store item page for other formats.