

HS14F-14M Cut Sheet



NITRA pneumatic threaded fitting, hose swivel, chrome-plated steel body, (1) 1/4in male NPT to (1) 1/4in female NPT.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HS14F-14M>

Technical Specifications

Brand	NITRA
Item	Fitting
Working Fluid	Air or inert gas
Fitting Connection Type	Threaded
Fitting Type	Hose swivel
Body Material	Chrome-plated steel
Fitting Measurement Type	SAE
Connection	(1) 1/4in male NPT and (1) 1/4in female NPT
Operating Pressure	145 psi
Operating Temperature	32 to 150 deg F

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document