


# HS4GH16A24 Cut Sheet



GC Valves solenoid coil, 24 VDC, 10W, 24in 18 AWG pigtail. For use with S201, NS201, S211 DC, NS211 DC, S301 and NS301 valves.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HS4GH16A24>

## Technical Specifications

<b>Brand</b>	GC Valves
<b>Item</b>	Solenoid coil
<b>Replacement</b>	No
<b>Voltage Rating</b>	24 VDC
<b>Power Rating</b>	10W
<b>Electrical Connection</b>	24in 18 AWG pigtail
<b>For Use With</b>	S201, NS201, S211 DC, NS211 DC, S301 and NS301 valves

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>