

# HS4GN16A24 Cut Sheet



GC Valves solenoid coil, 24 VDC, 10W, 24in 18AWG pigtail. For use with S201, NS201, S211 DC, NS211 DC, S301 and NS301 valves.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HS4GN16A24>

## Technical Specifications

Brand	GC Valves
Item	Solenoid coil
Replacement	No
Voltage Rating	24 VDC
Power Rating	10W
Electrical Connection	24in 18AWG pigtail
For Use With	S201, NS201, S211 DC, NS211 DC, S301 and NS301 valves

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>